TWO-COMPONENT GEL FILLERS FOR ELECTRICAL INSULATION AND SEALING



Fast cross-linking





Crystal clear

to keep visible the connection and the content of the enclosure



replaygel®

Repositionable

quickly reagglomerates even after first installation

APPLICATIONS

- Filling of junction boxes
- Insulation of electrical connections
- Insulation of electronic boards and components
- Protection of connections against weathering (rain, moisture), dust and intrusion of animals, bugs and leaves



May be partially used



High electrical insulation



High moisture protection



Re-enterable



Unlimited



Compliant to EU Directive 2015/863



Halogen free



Eco-friendly



NON-HAZARDOUS EU Reg. no. 1272/2008




Non-irritant



Odourless and solvent-free



Fast cross-linking re-enterable two-component gel filler for electrical insulation







Bottles

ref.	item	item volume min./mult. ord.qty. (cf)		watch video
MP0050	MPgel 50	0,5	12	国都英国 安海战组织
MP0100	MPgel 100	1	12	

CONTENTS

- Two separate clear bottles
- 1 litre graduated jug
- Stirring stick



Bags

ref.	item	volume (liters)	min./mult. ord.qty. (cf)	watch video
MP170	MPgel 170	0,170	4	
MP240	MPgel 200	0,200	4	
MP420	MPgel 420	0,420	4	
MP600	MPgel 600	0,600	4	

CONTENTS

- Bag with removable baffle
- Pouring spout with Perforation Pouring System (PPS)



Tanks	ref.	item	volume (liters)	min./mult. ord.qty. (cf)	watch video
	MP1000	MPgel 1000	10	1	

CONTENTS

- Two separate tanks
- 1 Litre graduated jug
- Stirring stick

crystalgel®

Crystal clear re-enterable two-component gel filler for electrical insulation



CONTENTS

- Two separate clear bottles
- 1 litre graduated jug

ref.	item	volume (liters)	min./mult. ord.qty. (cf)	watch video		
MP0200	CRYSTALGEL 1L	1	12	回数数回 9236次以		
MP2200	CRYSTALGEL 2L	2	12			

replaygel®

Repositionable re-enterable two-component gel filler for electrical insulation



Thanks to its innovative formulation, Replaygel® can be repositioned even long afterwards initial curing: Replaygel® easily and quickly reagglomerates while retaining its insulation a



CONTENTS

- Two separate clear bottles
- 1 Litre graduated jug

ref.	item	volume (liters)	min./mult. ord.qty. (cf)	watch video
MP3100	REPLAYLGEL 1L	1	12	